

scensibles®

"Scensibles System has worked wonderfully for us and it's one of the best things we've done to improve restroom appearance, odor control, and assurance of proper disposal."

— Don Sullivan, Manager of Custodial Services, University of Massachusetts at Amherst

Scensibles® Hygienic Disposal System For Menstrual Care Products

- Maintain clean-restroom standards with the complete Scensibles® disposal system
- Reduce or eliminate unpleasant odors while keeping offensive waste out of view
- Minimize exposure to possible blood-borne pathogens and harmful germs while ensuring safe and hygienic handling for custodial staff
- Provides an easy alternative to flushing products, especially tampons, down the toilet — saving on plumbing repair costs
- Scensibles® system can be used alone, or to complement existing stall waste receptacles

Scensibles® Personal Disposal Bags

- Single-use bag for sanitary pads, tampons, applicators, pantyliners and wipes
- Easy 4" handle-tie closures help completely conceal contents
- Bag gusset expands to hold bulky products
- Built-in antimicrobial agents inhibit the growth of odor-causing bacteria
- Interleave folded in refill box provides low-touch easy dispensing

Contemporary pattern masks the contents and helps eliminate odors with a pleasant fresh fragrance.



SDW

Scensibles® Dispensers

- Attractive and compact design
- Install with double-sided foam tape or screws (provided)
- Durable imprinted instructions
- Easy refilling

Scensibles® Universal Poly Receptacle Liners

- Leak proof
- Made of HDPE (LBSF500HD)
- Pleasant fresh fragrance
- Built-in antimicrobial agents inhibit the growth of odor causing bacteria
- SecureFit360® poly liners are ideal for high traffic restrooms such as airports, arenas, schools and more

Scensibles® poly liner bags can be used with most common surface or wall mount, and recessed receptacles. (See reference guide)

LBSF500HD
U.S. Patent No. 9,957,105



SecureFit360® poly liner bags are custom designed with a unique strap that wraps around the bottom of the receptacle to secure in place and enclose waste for fast, easy and safe removal. Strap keeps the bag tight fitting so it doesn't collapse inside the receptacle.

The 7.5 inch **wraparound strap** is used as a handle to eliminate the need to reach into receptacles to remove the liner. Simply pull up on the strap for safe removal of the contained and concealed contents.

HDi

1890 Chrysler Dr.
Belvidere, IL 61008
815-547-3737
sales@2hdi.com
www.HDi3.com